

BSA Self-Regulating Heating Cable



nVent RAYCHEM BSA self-regulating trace heating cables are an ideal solution for freeze protection of pipes and vessels and for process temperature maintenance, in non-hazardous industrial locations, without steam-cleaning requirement. They maintain process temperatures up to 65°C and can withstand intermittent exposure temperatures up to 85°C. BSA heating cables use the same heating core and polyolefin inner jacket as the BTV. The earth path consists of an aluminum foil wrap and metallic drain wires, providing 100% electrical protection coverage. The polyolefin outer jacket is suitable for mild inorganic solutions and provides excellent protection.

KENMERKEN

Foil wrap /drain-wire construction and modified polyolefin jackets provide a highly flexible cable

The unique construction allows stripping the jackets in no time, for fast connection

100% electrical earth path coverage for ultimate safety

Reliable long life performance with a 10 year product warranty available

SPECIFICATIES

Supply Voltage:	0 – 230 V
Ground Path Type:	Foil and Drainwire
Geleidermateriaal:	Nickel-Plated Copper
Area Classification:	Non-Hazardous
Outer Jacket Material:	Polyolefine

Table 1/1

Catalogusnummer	Naam van het item	Nominal Power Output @ 10°C, 230V	Max Circuit Length	Nominal Width	Nominal Thickness
P000002271	3BSA2-DR	10 W/m	150 m	13.7 mm	6.2 mm
P000002272	7BSA2-DR	23 W/m	120 m	13.7 mm	6.2 mm

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT