


PCB Solder Side Cover CPCI



A solder side cover protects the solder side of a PCB mechanically.

CERTIFICERINGEN



KENMERKEN

Cover is perforated for better cooling of components

Mechanical protection of solder side

SPECIFICATIES

Producttype:	Deksel
Werkt met:	Frontpanelen
Materiaal:	Kunststof
Type:	Afdekking soldeerzijde

Table 1/1


Catalogusnummer	Rekhoogte	Hoeveelheid in verpakking	Diepte (D)	Breedte (W)	Snelle verzending
24579-037	3U	1	160mm	100mm	Nee

Catalogusnummer	Rekhoogte	Hoeveelheid in verpakking	Diepte (D)	Breedte (W)	Snelle verzending
24579-039	6U	1	80mm	233.35mm	Nee
24579-038	6U	1	160mm	233.35mm	Nee

AANVULLENDE PRODUCTGEGEVENS

Fixing clips are required for mounting the perforated covers; please order separately.

DIAGRAMMEN



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE