

# Varistar CP Perforated Door, Seismic IP20, Multi-Point Locking

## Centrale d'électricité

IP 20 Seismic doors with reinforced and multi-point locking.

The multi-point locking helps achieve necessary contact to avoid EMI effects on electronics.

### CARACTÉRISTIQUES

Perforated door with Multi-Point locking for Seismic & IP 20 applications

Opening angle 180°

Lever handle with push button

### LES CARACTÉRISTIQUES TECHNIQUES

| Table 1/2           |             |         |         |            |            |                             |
|---------------------|-------------|---------|---------|------------|------------|-----------------------------|
| Référence catalogue | Rack Height | Hauteur | Largeur | Couleur    | Color Code | Conformité à                |
| 21630-876           | 33 U        | 1600 mm | 600 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-877           | 33 U        | 1600 mm | 800 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-878           | 38 U        | 1800 mm | 600 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-879           | 38 U        | 1800 mm | 800 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-880           | 42 U        | 2000 mm | 600 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-881           | 42 U        | 2000 mm | 800 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-882           | 47 U        | 2200 mm | 600 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |

| Référence catalogue | Rack Height | Hauteur | Largeur | Couleur    | Color Code | Conformité à                |
|---------------------|-------------|---------|---------|------------|------------|-----------------------------|
| 21630-883           | 47 U        | 2200 mm | 800 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |

Table 2/2

| Référence catalogue | Locking Type    | Matériau | Product Type | Protection Rating | Type                   | Fonctionne avec |
|---------------------|-----------------|----------|--------------|-------------------|------------------------|-----------------|
| 21630-876           | 4-Point Locking | Acier    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP     |
| 21630-877           | 4-Point Locking | Acier    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP     |
| 21630-878           | 4-Point Locking | Acier    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP     |
| 21630-879           | 4-Point Locking | Acier    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP     |
| 21630-880           | 4-Point Locking | Acier    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP     |
| 21630-881           | 4-Point Locking | Acier    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP     |
| 21630-882           | 5-Point Locking | Acier    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP     |
| 21630-883           | 5-Point Locking | Acier    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP     |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : [www.nvent.com](http://www.nvent.com) et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**