

# Internal segregation horizontal plates | Répartition de puissance, MSIS



This polycarbonate horizontal separation plate, MSIS, is available off the shelf and pre-sized. The plate should be used when subsections need to be segregated. It is placed between a mounting plate and a front panel that is placed inside the enclosure. No screws are needed, which makes mounting easy. The fix section can then comply to up to form 4 segregation according to IEC 61439.

## FONCTIONS

Description: Pre-sized horizontal separation plates between the mounting level and the front covers. Slides easily into place and let us to get Form 4 compartments for MCB's and MCCB's. No screws need.

Matériaux: 3 mm reinforced polycarbonate.

Livraison: 1 piece.

Polycarbonate horizontal separation plates, pre-sized to cover the space between the rear of subsections and front panels, in order to create compartments

The standard accessory is available off the shelf, and is pre-cut ready to be mounted into 600 or 800 mm wide enclosures

The plates can easily be mounted and do not require screws

Customer's required labour time is reduced as the plate is pre-cut and does not require screws for fixation, which in turn reduces their labour cost

The fix section can comply up to form 4 segregation according to IEC 61439, which is a necessary requirement for particular projects

The mounting plate (MSMPN) is to be fixed directly into the fix system vertical profiles (MSFP)

Partial panels (MSMBP or MSMPCP) are required in order to complete the fixed compartment

## SPÉCIFICATIONS

**Épaisseur:** 3mm  
**Couleur:** Gris  
**Matériaux:** Polycarbonate renforcé  
**Finition:** Lisse

Table 1/1

Référence catalogue	Largeur	Matériaux de l'armoire	Famille de produits	Expédition rapide
MSIS400	400mm	Acier doux	Autoportant	No
MSIS600	600mm	Acier doux	Autoportant	No
MSIS800	800mm	Acier doux	Autoportant	No

## AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur [www.nvent.com](http://www.nvent.com) et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.



Notre gamme complète de marques:

**CADDY    ERICO    HOFFMAN    ILSCO    SCHROFF    TRACHTE**

©2025 nVent. Toutes les marques et tous les logos nVent sont la propriété ou sont sous licence de nVent Services GmbH ou de ses sociétés affiliées. Toutes les autres marques déposées sont la propriété de leurs détenteurs respectifs. nVent se réserve le droit de modifier les spécifications sans préavis.

Ce document est généré par le système.