


Horizontal Perforated Strip

Energiebedrijven



Perforated strip out of 1mm Aluminum for centering shielded plug-in units.

CERTIFICERINGEN



KENMERKEN

For centering the shielded plug-in units

SPECIFICATIES

Table 1/2

Catalogusnummer	Rack Width	Package Quantity	Lengte	Materiaal	Product Family	Product Type
30845-253	84 HP	1	431.6 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Perforated Strip

Catalogusnummer	Rack Width	Package Quantity	Lengte	Materiaal	Product Family	Product Type
30845-197	28 HP	1	147.12 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Perforated Strip
30845-211	42 HP	1	218.24 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Perforated Strip
30845-232	63 HP	1	324.92 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Perforated Strip

Table 2/2

Catalogusnummer	Works With
30845-253	Subracks, Cases
30845-197	Subracks, Cases
30845-211	Subracks, Cases
30845-232	Subracks, Cases

ADDITIONAL PRODUCT DETAILS

Only usable with double-T threaded insert.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of

opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE