

ACS-30 User Interface Terminal



nVent RAYCHEM ACS-UIT3 is a user interface terminal used together with the ACS-PCM2-5 panel in the ACS-30 system. With large LCD touch-screen display, it provides easy programming without keyboards or cryptic labels.

KENMERKEN

Simple to install and operate, with large touch screen display

Alarm outputs

Multiple communications ports (RS-485, RS-232, or 10/100Base-T Ethernet)

BACnet to Modbus protocol gateways, with Modbus registries pre-programmed

USB interface, for easy configuration and firmware upgrades

Reliable during long life: 2 year product warranty available, maintenance free

SPECIFICATIES

Table 1/2

Catalogusnummer	Artikelnaam	Voedingsspanning	Weergeven	Materiaal	IP-classificatie	Hoogte
10332-039	ACS-UIT3 REPLACEMENT UNIT	10 – 36 V	12-inch touchscreen, TFT LCD	FRP	IP20	245 mm
1244-022626	ACS-30-EU-UIT3	100 – 240 V	12-inch touchscreen, TFT LCD	FRP	IP65	400 mm

Table 2/2

Catalogusnummer	Artikelnaam	Breedte	Diepte
10332-039	ACS-UIT3 REPLACEMENT UNIT	306 mm	63 mm

Catalogusnummer	Artikelnaam	Breedte	Diepte
1244-022626	ACS-30-EU-UIT3	400 mm	210 mm

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Ons krachtige merkenportfolio:

RAYCHEM PYROTENAX TRACER NUHEAT