

Elexant 450c Control Unit



nVent RAYCHEM Elexant 450c is the next generation touch screen heat tracing controller for dual independent heating zone control, with multiple integrated sensing modes and remote alarm capability, providing the most energy efficient pipe freeze protection and temperature maintenance control system.

KENMERKEN

Elexant 450c with Modbus RS485 port for remote monitoring connectivity, configuration, and ease of integration in a Building Management System (BMS).

Intuitive set-up and programming of the unit with a 4.3" color touch screen

Controls 2 independent heating circuits

Alarm relay with change over contact to signal power, temperature or communication problems

Pipe temperature monitoring with high and low temperature alarm

Heating system diagnostic data maintained in a logged file for easy download

USB port for preset-up in power off mode and firmware upgrade

Reliable during long life: 6 year extended product warranty available

SPECIFICATIES

Output Relay:	2 x 4 A @ 230 VAC
Sensor Cable Length:	5 m
Diepte:	56 mm
Hoogte:	110 mm
Breedte:	158 mm
Supply Voltage:	195 – 253 V
Temperature Control Range:	0 – 85 °C
Montage:	DIN Rail
IP-classificatie:	IP20
Sensor Type:	NTC, 2K Ω @ 25°C
Alarm Relay:	Single Pole Double Throw Relay, Voltage-free, Rating 2 A @ 250 VAC

Table 1/1

Catalogusnummer	Naam van het item	Communication Protocol
1244-021970	ELEXANT 450c	Geen
1244-022623	ELEXANT 450c-Modbus	Modbus RTU

ADDITIONAL PRODUCT DETAILS

Temperature Control Range, (Line Sensing) can be extended to 250° using the Elexant 450 Plug-In Sensor Module and PT100 sensor

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT