

NRG-DM Digital Timer Thermostat



nVent RAYCHEM NRG-DM is a digital timer thermostat for electrical floor heating equipped with a large display and intuitive software. Eco Design compliant thanks to the following functions: Adaptive start control. For more details, please consult the Commissioning sheet (INST324 or EU2550).

KENMERKEN

Easy to use, intuitive navigation: large LCD display with blue back light

3 operating modes: event mode or weekly schedule to reduce energy; boost mode or temporary override; constant mode

Energy efficient adaptive function

Optimum heat management, with 4 sensor modes

Reliable during long life: 12 year total care warranty available, maintenance free

SPECIFICATIES

Table 1/5

Catalogusnummer	Naam van het item	Power Supply	Measuring Range	Adjustable Differential	Regulation Type	Max Contact Voltage
1244-015152	R-NRG-DM	230 V	5 – 40 °C	Nee	On/Off	230 V

Table 2/5

Catalogusnummer	Naam van het item	Max Contact Load	Sensor/Feeler Type	Temperature Control Class	Control Characteristic	Remote Operation
1244-015152	R-NRG-DM	13 A	Resistance Sensor	IV	PID	Nee

Table 3/5

Catalogusnummer	Naam van het item	Switching Program Quantity	Power Consumption, Standby	IP-classificatie	RAL Number	Kleur

1244-015152	R-NRG-DM	7	0.4 W	IP21	9010	Clear White
-------------	----------	---	-------	------	------	-------------

Table 4/5

Catalogusnummer	Naam van het item	IFTTT Support Available	Clock Type	Clock Model	Self Learning	Hoogte
1244-015152	R-NRG-DM	Nee	Day Clock	Digitaal	Ja	82 mm

Table 5/5

Catalogusnummer	Naam van het item	Breedte	Diepte
1244-015152	R-NRG-DM	82 mm	40 mm

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT