

Polymer Junction Box For PI Cables



nVent RAYCHEM JB-EX-XX are junction boxes with or without earth plate and external earth stud. Depending on the type, they are equipped with 10 mm² or 35 mm² terminals to allow loads up to 100 A to a power supply or other configurations such as Tees or Splices. Available in different sizes with a various number of M20 entries to accommodate multiple configurations and electrical loads.

KENMERKEN

Simple and fast to install, easy to maintain

Hazardous areas approved

Available in different models and sizes for multiple configurations

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIES

Area Classification:	Non-Hazardous; Hazardous
IP-classificatie:	IP66
Montage:	Wall/Support Bracket Mounted
Ambient Temperature:	-55 tot 55 °C

Table 1/2

Catalogusnummer	Naam van het item	Max Voltage	Cable Entry	Max Conductor Cross Section	Hoogte	Breedte
1244-006384	JB-EX-20-EP	590 V	1xM25 3xM20	10 mm ²	120 mm	122 mm
1244-000579	JB-EX-21	550 V	1xM32 6xM20	10 mm ²	160 mm	160 mm
1244-000590	JB-EX-20	590 V	1xM25 3xM20	10 mm ²	120 mm	122 mm
1244-006653	JB-EX-21/35MM2	690 V	1xM40 6xM20	35 mm ²	160 mm	260 mm

Table 2/2

Catalogusnummer	Naam van het item	Diepte	Light Indication Included	Earth Plate Included
1244-006384	JB-EX-20-EP	90 mm	Nee	Ja
1244-000579	JB-EX-21	90 mm	Nee	Nee
1244-000590	JB-EX-20	90 mm	Nee	Nee
1244-006653	JB-EX-21/35MM2	90 mm	Nee	Nee

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT