


E650C-R Gutter Sensor for Elexant 650c-Modbus



Rod-shaped sensor E650C-R for combined measurement of temperature and moisture values in gutters and neighbouring areas, such as flat roofs and downpipes to be used with Elexant 650c-Modbus. Robust version made of brass, fully encapsulated. Extremely compact design with axial cable outlet and threaded bolt for fixing in position. Optional mounting plate for sensor E650C-R can be used with sensor height adjustment above the mounting surface. The mounting plate can be matched to the mounting location by bending and then attached by gluing or soldering. Two material versions are available for suitable material combinations in gutter and flat roof applications.

FONCTIONS

Cable connection: Axial

Connection cable: 4 x 0.5 mm²

Temperature range for moisture measurement: -20°C to 30°C

SPÉCIFICATIONS

Table 1/2

Référence catalogue	Nom de l'élément	Communication	Profondeur	Zone explosible	Hauteur	Classe d'étanchéité IP
1244-022799	E650C-R-BRACKET-CU	Non	80 mm	Non	2 mm	IP68
1244-022798	E650C-R-BRACKET-ZN	Non	80 mm	Non	2 mm	IP68
1244-022795	E650C-R	Non	96 mm	Non	14 mm	IP68

Table 2/2

Référence catalogue	Nom de l'élément	Plage de mesures	Largeur
1244-022799	E650C-R-BRACKET-CU		132 mm

Référence catalogue	Nom de l'élément	Plage de mesures	Largeur
1244-022798	E650C-R-BRACKET-ZN		132 mm
1244-022795	E650C-R	-20 to 30 °C	14 mm

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Notre gamme complète de marques:

RAYCHEM PYROTENAX TRACER NUHEAT