


Combined Mounting Kit for Chassis



The combined mounting enable the option to split a 6 U high subrack or case in 2 x 3 U and 6 U sections. Different versions are available.

CERTIFICERINGEN



KENMERKEN

Designed to accept Euroboards (100 mm high) and double Euroboards (233.35 mm high)

Subdivision of the 6 U assembly area into: 2 x 3 U, 1 x 6 U

SPECIFICATIES

Rekhoogte:	6U
Type:	Gecombineerd
Productserie:	EuropacPRO
Producttype:	Montageset
Werkt met:	Subracks

Table 1/1

Catalogusnummer	Hoeveelheid in verpakking	Rekbreedte 1	Rekbreedte 2	Materiaal	Snelle verzending
24562-440	1	40HP	42HP	Aluminium, Zinklegering	Nee
24562-442	1	42HP	40HP	Aluminium, Zinklegering	Nee
24562-484	1	84HP		Aluminium, Zinklegering	Nee

Catalogusnummer	Hoeveelheid in verpakking	Rekbreedte 1	Rekbreedte 2	Materiaal	Snelle verzending
24562-420	1	20HP	62HP	Aluminium, Zinklegering	Nee
24562-463	1	63HP	19HP	Aluminium, Zinklegering	Nee

AANVULLENDE PRODUCTGEGEVENS

Please order separately: Front panel 6 U, 2 HP to cover the strut.

The following guide rails cannot be used: type "accessory", type "accessory, strengthened" and type "for 4.4" PCB".

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE