We connect and protect

# Socket Strip, IEC, 3-Phase

## Centrale d’électricité

Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C13 and C19 outlets with 3 phase input.

## CERTIFICATIONS

RoHS COMPLIANT

EAC

## CARACTÉRISTIQUES

- Socket strips with IEC sockets in accordance with IEC 60320
- Vertical mounting
- Socket strips can be rotated through all four directions (in 90° increments) during installation
- Connecting cable 2 m
- Mounting height 1 U

## LES CARACTÉRISTIQUES TECHNIQUES

Table 1/2

| Référence catalogue | Socket Type | Tension CA | Couleur | Profondeur | Hauteur | Longueur |
|---|---|---|---|---|---|---|
| 60110-284 | IEC C13, IEC C19 | 400 V | Grey, Black, Red | 44 mm | 44 mm | 947.5 mm |
| 60110-285 | IEC C13, IEC C19 | 400 V | Grey, Black, Red | 44 mm | 44 mm | 1753 mm |

| Référence catalogue | Socket Type | Tension CA | Couleur | Profondeur | Hauteur | Longueur |
|---|---|---|---|---|---|---|
| 60110-283 | IEC C13 | 400 V | Grey, Black, Red | 44 mm | 44 mm | 947.5 mm |

Table 2/2

| Référence catalogue | Product Type |
|---|---|
| 60110-284 | Socket Strip |
| 60110-285 | Socket Strip |
| 60110-283 | Socket Strip |

## ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

## AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.