

Front Panel, Unshielded, With Fastener Pin

Centrale d'électricité



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

CERTIFICATIONS



CARACTÉRISTIQUES

Enable grounding of the front area (protection class 1)

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/3						
Référence catalogue	Rack Width	Package Quantity	Montage	Front Finish	Rear Finish	Treated Edges
20119-161	21 HP	1	Screw-on Front	Anodisé	Conductive	Non
20119-163	42 HP	1	Screw-on Front	Anodisé	Anodisé	Non
20119-162	28 HP	1	Screw-on Front	Anodisé	Conductive	Non
20119-160	14 HP	1	Screw-on Front	Anodisé	Conductive	Non

Référence catalogue	Rack Width	Package Quantity	Montage	Front Finish	Rear Finish	Treated Edges
20119-159	7 HP	1	Screw-on Front	Anodisé	Conductive	Non

Table 2/3

Référence catalogue	Conformité à	EMC Shielding	Hauteur	Matériau	Product Type	Rack Height
20119-161	IEC 60297-3-101, IEEE 1101.1/10	Non	128.4 mm	Aluminium	Panneau avant	3 U
20119-163	IEC 60297-3-101, IEEE 1101.1/10	Non	128.4 mm	Aluminium	Panneau avant	3 U
20119-162	IEC 60297-3-101, IEEE 1101.1/10	Non	128.4 mm	Aluminium	Panneau avant	3 U
20119-160	IEC 60297-3-101, IEEE 1101.1/10	Non	128.4 mm	Aluminium	Panneau avant	3 U
20119-159	IEC 60297-3-101, IEEE 1101.1/10	Non	128.4 mm	Aluminium	Panneau avant	3 U

Table 3/3

Référence catalogue	Type	Largeur
20119-161	Front Panel without Handle	106.3 mm
20119-163	Front Panel without Handle	213 mm
20119-162	Front Panel without Handle	141.9 mm
20119-160	Front Panel without Handle	70.8 mm
20119-159	Front Panel without Handle	35.2 mm

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE