

PSU 19" AC/DC Maxpower 100 W, Triple



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and three output voltages.

CERTIFICERINGEN



KENMERKEN

Wide input voltage range 90 ... 254 V AC and 100 ... 360 VDC with active power-factor correction (PFC)

3 output voltages

Signalling: Output voltage OK

High power density

SPECIFICATIES

Table 1/3

Catalogusnummer	Type	Ingangsspanning AC	Voeding	Aantal uitgangsspanningen	Spanning 1	Stroom 1
13100-122	19 inch geschakeldeodus	90 – 264V	100W	3	5V	8A
13100-123	19 inch geschakeldeodus	90 – 264V	100W	3	5V	8A

Table 2/3

Catalogusnummer	Spanning 2	Stroom 2	Spanning 3	Stroom 3	Rekhoogte	Rekbreedte
13100-122	12V	2.5A	12V	2.5A	3U	8HP
13100-123	15V	2A	15V	2A	3U	8HP

Table 3/3

Catalogusnummer	Diepte	Hoeveelheid in verpakking	Snelle verzending
13100-122	171.93mm	1	Nee
13100-123	171.93mm	1	Nee

AANVULLENDE PRODUCTGEGEVENS

Please order front panel separately.

Output data at mains voltage > 190 VAC, Ta = -25 ... 50 °C.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE