

Kit materiale riempitivo orizzontale serie T.



T-Series horizontal filler material kits contain the following: Filler material, two horizontal packings, pouring basin ceramic guide tube and pouring basin crucible ceramic and disk. All filler material kits contain one-time use components that are sized to a specific sleeve, pouring basin and pouring basin crucible combination. Ordering filler material kits simplifies ordering, reduces order errors and helps ensure proper sizing of components.

CARATTERISTICHE

Simplifies ordering

Used to splice the same diameter bars

All components are for one-time use

SPECIFICHE

Table 1/1

Codice a catalogo	Dimensione armatura, metrica	Dimensioni armatura, USA	Dimensioni armatura, Canada
RBT121018HB	38 mm	# 12	
RBT5101HB	16 mm	# 5	15 MLN
RBT6101HB	20 mm	# 6	20 MLN
RBT7101HB	22 mm	# 7	
RBT8101HB	25 mm	# 8	25 MLN
RBT81011HB	25 mm	# 8	25 MLN
RBT9101HB	28 mm	#9	30 MLN

Codice a catalogo	Dimensione armatura, metrica	Dimensioni armatura, USA	Dimensioni armatura, Canada
RBT91011HB	28 mm	#9	30 MLN
RBT1091HB	32 mm	# 10	
RBT11101HB	36 mm	#11	35 MLN
RBT14101HB	43 mm	#14	45 MLN
RBT1891HB	57 mm	# 18	55 MLN


INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

Filler material kits are a component in splice kits. Care should be taken to avoid duplication of orders.

Components can also be purchased separately: (1) Filler Material, (2) Packing, (3) Pouring Basin Ceramic Guide Tube, and (4) Pouring Basin Ceramic Insert and Disk.

Filler Material Kit Components				
Filler Material Kit	Filler Material	Packing (2 Required)	Pouring Basin Ceramic Insert and Disk	Pouring Basin Ceramic Guide Tube
RBT5101HB	RBF40	RBS354710	RBS5037	RBS5038
RBT6101HB	RBF50	RBS35477	RBS5037	RBS5038
RBT7101HB	RBF50	RBS35478	RBS5037	RBS5038
RBT81011HB	RBF70	RBS354710	RBS5037	RBS5038
RBT8101HB	RBF55	RBS354710	RBS5037	RBS5038
RBT91011HB	RBF90	RBS354711	RBS5037	RBS5038
RBT9101HB	RBF80	RBS354711	RBS5037	RBS5038
RBT1091HB	RBF90	RBS354712	RBS5037	RBS5038
RBT11101HB	RBF105	RBS354712	RBS5037	RBS5038
RBT121018HB	RBF180	RBS354715	RBS5037	RBS5038
RBT14101HB	RBF195	RBS354715	RBS5037	RBS5039
RBT1891HB	RBF270	RBS354720	RBS5037	RBS5039



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

Nord America

+1.800.753.9221

Opzione 1 – Assistenza
clienti

Opzione 2 – Assistenza
tecnica

Europa

Paesi Bassi:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Germania:

800 1890272

altri paesi:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Il nostro straordinario portafoglio di marchi:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE