


EuropacPRO 19" Subrack Kit for Railway, Retrofit Shielding, SNCF

Servizi di distribuzione di energia

Subrack for Railway applications, conform to SNCF Standard, non-shielded versions.



CERTIFICAZIONI



CARATTERISTICHE

SNCF listed, EuropacPRO-fer, tested to NF F 61-005 and NF F 60-002

The 19" bracket is firmly fixed to the side panel (tox-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

Lateral support bars to NFF standard facilitate insertion of subrack into the (cabinet) frame. The double 19" screwing position adds to additionally safety (NFF standard)

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Aluminum construction

Horizontal rail type "Heavy"

SPECIFICHE

Table 1/3

Numero catalogo	Rack Height	Rack Width	Profondità	Package Quantity	For Mounting	Board Depth
21500-027	6 U	84 HP	320 mm	1	Backplane	220 mm
21500-029	3 U	84 HP	320 mm	1	Backplane	220 mm
21500-067	3 U	36 HP	320 mm	1	Backplane	220 mm
21500-070	6 U	36 HP	320 mm	1	Backplane	220 mm

Table 2/3

Numero catalogo	EMC Gasket Type	Shock and Vibration Tolerance	Handle Included	Montaggio	È conforme a	EMC Shielding
21500-027	Textile	5 g (force)	Sì.	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	No
21500-029	Textile	5 g (force)	Sì.	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	No
21500-067	Textile	5 g (force)	Sì.	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	No
21500-070	Textile	5 g (force)	Sì.	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	No

Table 3/3

Numero catalogo	Product Type	Carico statico	Certificazioni
21500-027	Subrack/Chassis	15 kgf	RoHS, SNCF
21500-029	Subrack/Chassis	15 kgf	RoHS, SNCF
21500-067	Subrack/Chassis	15 kgf	RoHS

Numero catalogo	Product Type	Carico statico	Certificazioni
21500-070	Subrack/Chassis	15 kgf	RoHS

ADDITIONAL PRODUCT DETAILS

Test reports are available online.

Fer = ferroviaire = French Railways, 1 T = 4 HP = 20.32 mm Receptacle/mounting frame for subracks, stainless steel, 9 T or 21 T on request.

Receptacle/mounting frame for subracks, stainless steel, 9 T or 21 T on request.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE