


EuropacPRO Mounting Plate for Use With Cover Plate

Servizi di distribuzione di energia



Mounting plate for use with cover plates for installation and fixing of heavy components. Full width mounting plates (as wide as the subrack or the system case) are fixed to the side panels. The partial width mounting plates are fixed to the side panel and horizontal rail by means of an assembly strip.

Guide rails Type 4,4" and type strengthened cannot be used in combination with a mounting plate. Top / bottom cover which will be inserted into the groove of the light (type L) horizontal rails cannot be used in combination with a mounting plate.

CERTIFICAZIONI



CARATTERISTICHE

For installation and fixing of heavy components

Mounting plate, full width: The mounting plate is as wide as the subrack/system case and is fixed to the side panels

A guide rail can be fitted in first and last slot position

In addition to the mounting plate EMC cover plates can also be fitted to the subrack

Guide rails type 4.4 and "strengthened" cannot be used

SPECIFICHE

Table 1/2

Numero catalogo	Rack Width	Package Quantity	Profondità	Materiale	Product Family	Product Type
34563-019	63 HP	1	172.5 mm	Alluminio	EuropacPRO	Mounting Plate

Numero catalogo	Rack Width	Package Quantity	Profondità	Materiale	Product Family	Product Type
34563-001	28 HP	1	112.5 mm	Alluminio	EuropacPRO	Mounting Plate
34563-003	63 HP	1	112.5 mm	Alluminio	EuropacPRO	Mounting Plate
34563-044	84 HP	1	412.5 mm	Alluminio	EuropacPRO	Mounting Plate
34563-042	84 HP	1	352.5 mm	Alluminio	EuropacPRO	Mounting Plate
34563-009	28 HP	1	172.5 mm	Alluminio	EuropacPRO	Mounting Plate
34563-002	42 HP	1	112.5 mm	Alluminio	EuropacPRO	Mounting Plate
34563-028	84 HP	1	292.5 mm	Alluminio	EuropacPRO	Mounting Plate
34563-026	84 HP	1	232.5 mm	Alluminio	EuropacPRO	Mounting Plate
34563-014	42 HP	1	172.5 mm	Alluminio	EuropacPRO	Mounting Plate
34563-024	84 HP	1	172.5 mm	Alluminio	EuropacPRO	Mounting Plate
34563-004	84 HP	1	112.5 mm	Alluminio	EuropacPRO	Mounting Plate

Table 2/2			
Numero catalogo	Larghezza	Works With	Certificazioni
34563-019	324.67 mm	Subracks	RoHS
34563-001	146.88 mm	Subracks	RoHS
34563-003	324.67 mm	Subracks	RoHS
34563-044	431.35 mm	Subracks	
34563-042	431.35 mm	Subracks	
34563-009	146.88 mm	Subracks	RoHS

Numero catalogo	Larghezza	Works With	Certificazioni
34563-002	217.99 mm	Subracks	RoHS
34563-028	431.35 mm	Subracks	
34563-026	431.35 mm	Subracks	
34563-014	217.99 mm	Subracks	RoHS
34563-024	431.35 mm	Subracks	RoHS
34563-004	431.35 mm	Subracks	RoHS

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE