


EuropacPRO Cover Plate for Bolting to Side Panel

Power Utilities



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be screwed onto the side panel.

SERTIFISERINGER



FUNKSJONER

For variable positioning of horizontal rails e.g. for PCBs with standard formats

Perforation degree 58%

Suitable for use with all horizontal rails

SPESIFIKASJONER

Table 1/2

Katalognummer	Rackbredde	Dybde	Pakkeantall	Produktfamilie	Produkttype	Type
24560-064	42 HP	175 mm	1	EuropacPRO	Dekselplate	Perforert
24560-065	42 HP	235 mm	1	EuropacPRO	Dekselplate	Perforert

Katalognummer	Rackbredde	Dybde	Pakkeantall	Produktfamilie	Produkttype	Type
24560-066	42 HP	295 mm	1	EuropacPRO	Dekselplate	Perforert
24560-071	63 HP	175 mm	1	EuropacPRO	Dekselplate	Perforert
24560-072	63 HP	235 mm	1	EuropacPRO	Dekselplate	Perforert
24560-073	63 HP	295 mm	1	EuropacPRO	Dekselplate	Perforert
24560-078	84 HP	175 mm	1	EuropacPRO	Dekselplate	Perforert
24560-079	84 HP	235 mm	1	EuropacPRO	Dekselplate	Perforert
24560-080	84 HP	295 mm	1	EuropacPRO	Dekselplate	Perforert
24560-081	84 HP	355 mm	1	EuropacPRO	Dekselplate	Perforert
24560-082	84 HP	415 mm	1	EuropacPRO	Dekselplate	Perforert
24560-083	84 HP	475 mm	1	EuropacPRO	Dekselplate	Perforert
24560-061	42 HP	275 mm	1	EuropacPRO	Dekselplate	Perforert
24560-062	63 HP	275 mm	1	EuropacPRO	Dekselplate	Perforert
24560-063	84 HP	275 mm	1	EuropacPRO	Dekselplate	Perforert
24579-090	42 HP	277.75 mm	1	EuropacPRO	Dekselplate	Perforert
24579-092	84 HP	277.75 mm	1	EuropacPRO	Dekselplate	Perforert

Table 2/2

Katalognummer	Arbeider med	Pakkeenhet	Tiltrekkingsmoment
24560-064	Subracks	Par.	2.1 N·m
24560-065	Subracks	Par.	2.1 N·m

Katalognummer	Arbeider med	Pakkeenhet	Tiltrekkingsmoment
24560-066	Subracks	Par.	2.1 N·m
24560-071	Subracks	Par.	2.1 N·m
24560-072	Subracks	Par.	2.1 N·m
24560-073	Subracks	Par.	2.1 N·m
24560-078	Subracks	Par.	2.1 N·m
24560-079	Subracks	Par.	2.1 N·m
24560-080	Subracks	Par.	2.1 N·m
24560-081	Subracks	Par.	2.1 N·m
24560-082	Subracks	Par.	2.1 N·m
24560-083	Subracks	Par.	2.1 N·m
24560-061	Subracks	Par.	
24560-062	Subracks	Par.	
24560-063	Subracks	Par.	
24579-090	Subracks	Par.	2.1 N·m
24579-092	Subracks	Par.	2.1 N·m

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE