

Interscale Fan Holder With Fans

Servizi di distribuzione di energia

Interscale Fan Holder With Fans, for desktop cases and 19" chassis. Available in different sizes and with three fan versions, with a air flow volume from 10 to 170 m³/h.

CARATTERISTICHE

Fan holder for mounting on bottom of case

Fans are simple to fit to the fan holder using vibration-damping fixing material

Fan holders fix into desktop case with 2 plastic feet or into 19" case with 2 screws

Fan holder cannot be used in conjunction with the mounting plate (instead use mounting plate with integrated fan holder)

For technical data of fans, please see delivery includes

SPECIFICHE

Table 1/3

Numero catalogo	Larghezza	Profondità	Package Quantity	Max Static Pressure	Max Ambient Temperature	Airflow
24828-105	40 mm	20 mm			70 °C	10 m³/h
24828-107	40 mm	20 mm			70 °C	10 m³/h
24828-104	40 mm	20 mm			70 °C	10 m³/h
24828-205	80 mm	25 mm			70 °C	19 m³/h
24828-207	80 mm	25 mm			70 °C	19 m³/h
24828-204	80 mm	25 mm			70 °C	19 m³/h
24830-102	80 mm	25 mm	2			

Numero catalogo	Larghezza	Profondità	Package Quantity	Max Static Pressure	Max Ambient Temperature	Airflow
24828-305	119 mm	25 mm			70 °C	170 m³/h
24828-307	119 mm	25 mm			70 °C	170 m³/h
24830-101	80 mm	25 mm		95.41 Pa	70 °C	109 m³/h

Table 2/3						
Numero catalogo	Noise Level	Altezza	Input Voltage DC	Potenza	Product Family	Product Type
24828-105	18 dB(A)	40 mm	12 V min	0.9 W	Interscale	Fan Unit
24828-107	18 dB(A)	40 mm	12 V min	0.9 W	Interscale	Fan Unit
24828-104	18 dB(A)	40 mm	12 V min	0.9 W	Interscale	Fan Unit
24828-205	32 dB(A)	80 mm	12 V min	2 W	Interscale	Fan Unit
24828-207	32 dB(A)	80 mm	12 V min	2 W	Interscale	Fan Unit
24828-204	32 dB(A)	80 mm	12 V min	2 W	Interscale	Fan Unit
24830-102		80 mm	12 V min			Fan Unit
24828-305	43 dB(A)	119 mm	12 V min	5.3 W	Interscale	Fan Unit
24828-307	43 dB(A)	119 mm	12 V min	5.3 W	Interscale	Fan Unit
24830-101	44.62 dB(A)	80 mm	12 V min			Fan Unit

Table 3/3	
Numero catalogo	Tipo
24828-105	Fan Tray
24828-107	Fan Tray

Numero catalogo	Tipo
24828-104	Fan Tray
24828-205	Fan Tray
24828-207	Fan Tray
24828-204	Fan Tray
24830-102	Fan Tray
24828-305	Fan Tray
24828-307	Fan Tray
24830-101	Fan Tray

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE