


Front Handle One-Piece, Width 12,2 mm

Strømforsyning



The handle can be assembled to a subrack or 19" front panel. Available with clear or black anodized surface. Handles will be bolted from the rear side.

SERTIFISERINGER



FUNKSJONER

Static load-carrying capacity 30 kg/pair

Bolted from rear

SPESIFIKASJONER

Table 1/2

Katalognummer	Rack Height	Package Quantity	Handle Type	Farge	Materiell	Product Family
10501-116	1 U	1	Rett	Silver	Aluminium	EuropacPRO
10501-004	2 U	1	Rett	Silver	Aluminium	EuropacPRO
10501-020	3 U	1	Angled Handle	Silver	Aluminium	EuropacPRO

Katalognummer	Rack Height	Package Quantity	Handle Type	Farge	Materiell	Product Family
10501-026	3 U	1	Rett	Sort	Aluminium	EuropacPRO
10501-005	3 U	1	Rett	Silver	Aluminium	EuropacPRO
10501-006	4 U	1	Rett	Silver	Aluminium	EuropacPRO
10501-007	5 U	1	Rett	Silver	Aluminium	EuropacPRO
10501-022	6 U	1	Angled Handle	Silver	Aluminium	EuropacPRO
10501-029	6 U	1	Rett	Sort	Aluminium	EuropacPRO
10501-008	6 U	1	Rett	Silver	Aluminium	EuropacPRO
10501-016	2 U	1	Rett	Silver	Aluminium	EuropacPRO
10501-021	4 U	1	Angled Handle	Silver	Aluminium	EuropacPRO
10501-018	4 U	1	Rett	Silver	Aluminium	EuropacPRO
10501-025	2 U	1	Rett	Sort	Aluminium	EuropacPRO
10501-027	4 U	1	Rett	Sort	Aluminium	EuropacPRO
10501-028	5 U	1	Rett	Sort	Aluminium	EuropacPRO

Table 2/2

Katalognummer	Product Type	Fungerer med	Dreiemoment
10501-116	Handle	Subracks	
10501-004	Handle	Subracks	
10501-020	Handle	Subracks	2.4 N·m
10501-026	Handle	Subracks	2.4 N·m

Katalognummer	Product Type	Fungerer med	Dreiemoment
10501-005	Handle	Subracks	2.4 N·m
10501-006	Handle	Subracks	
10501-007	Handle	Subracks	
10501-022	Handle	Subracks	2.4 N·m
10501-029	Handle	Subracks	2.4 N·m
10501-008	Handle	Subracks	2.4 N·m
10501-016	Handle	Subracks	
10501-021	Handle	Subracks	2.4 N·m
10501-018	Handle	Subracks	2.4 N·m
10501-025	Handle	Subracks	
10501-027	Handle	Subracks	
10501-028	Handle	Subracks	

ADDITIONAL PRODUCT DETAILS

Please order assembly part kit separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE