


Horizontal Perforated Strip

Power Utilities



Perforated strip out of 1mm Aluminum for centering shielded plug-in units.

SERTIFISERINGER



FUNKSJONER

For centering the shielded plug-in units

SPESIFIKASJONER

Table 1/2

Katalognummer	Rackbredde	Pakkeantall	Lengde	Materiale	Produktfamilie	Produkttype
30845-232	63 HP	1	324.92 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO LUFT, CompacPRO, PropacPRO, InPac	Perforert stripe

Katalognummer	Rackbredde	Pakkeantall	Lengde	Materiale	Produktfamilie	Produkttype
30845-197	28 HP	1	147.12 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO LUFT, CompacPRO, PropacPRO, InPac	Perforert stripe
30845-211	42 HP	1	218.24 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO LUFT, CompacPRO, PropacPRO, InPac	Perforert stripe
30845-253	84 HP	1	431.6 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO LUFT, CompacPRO, PropacPRO, InPac	Perforert stripe

Table 2/2

Katalognummer	Arbeider med
30845-232	Subracks, Tilfeller
30845-197	Subracks, Tilfeller
30845-211	Subracks, Tilfeller
30845-253	Subracks, Tilfeller

YTTERLIGERE PRODUKTDETALJER

Only usable with double-T threaded insert.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk,

feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE