

Varistar CP Swing Frame for 800 mm Width

Servizi di distribuzione di energia

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° / 160° movement and flexible pivot point.

CARATTERISTICHE

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks

120° / 160° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

SPECIFICHE

Table 1/2

Numero catalogo	Rack Height	Colore	Color Code	Altezza	Materiale	Product Type
21630-669	24 U	Black Grey	RAL 7021	1200 mm	Acciaio	Cabinet/Rack Frame
21630-680	24 U	Black Grey	RAL 7021	1200 mm	Acciaio	Cabinet/Rack Frame
21630-671	29 U	Black Grey	RAL 7021	1400 mm	Acciaio	Cabinet/Rack Frame
21630-681	29 U	Black Grey	RAL 7021	1400 mm	Acciaio	Cabinet/Rack Frame
21630-673	33 U	Black Grey	RAL 7021	1600 mm	Acciaio	Cabinet/Rack Frame
21630-682	33 U	Black Grey	RAL 7021	1600 mm	Acciaio	Cabinet/Rack Frame
21630-675	38 U	Black Grey	RAL 7021	1800 mm	Acciaio	Cabinet/Rack Frame

Numero catalogo	Rack Height	Colore	Color Code	Altezza	Materiale	Product Type
21630-683	38 U	Black Grey	RAL 7021	1800 mm	Acciaio	Cabinet/Rack Frame
21630-677	42 U	Black Grey	RAL 7021	2000 mm	Acciaio	Cabinet/Rack Frame
21630-684	42 U	Black Grey	RAL 7021	2000 mm	Acciaio	Cabinet/Rack Frame
21630-679	47 U	Black Grey	RAL 7021	2200 mm	Acciaio	Cabinet/Rack Frame
21630-685	47 U	Black Grey	RAL 7021	2200 mm	Acciaio	Cabinet/Rack Frame

Table 2/2

Numero catalogo	Protection Rating	Larghezza
21630-669	IP20	800 mm
21630-680	IP20	800 mm
21630-671	IP20	800 mm
21630-681	IP20	800 mm
21630-673	IP20	800 mm
21630-682	IP20	800 mm
21630-675	IP20	800 mm
21630-683	IP20	800 mm
21630-677	IP20	800 mm
21630-684	IP20	800 mm
21630-679	IP20	800 mm
21630-685	IP20	800 mm

ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE