

E650C-R Gutter Sensor for Elexant 650c-Modbus



Rod-shaped sensor E650C-R for combined measurement of temperature and moisture values in gutters and neighbouring areas, such as flat roofs and downpipes to be used with Elexant 650c-Modbus. Robust version made of brass, fully encapsulated. Extremely compact design with axial cable outlet and threaded bolt for fixing in position. Optional mounting plate for sensor E650C-R can be used with sensor height adjustment above the mounting surface. The mounting plate can be matched to the mounting location by bending and then attached by gluing or soldering. Two material versions are available for suitable material combinations in gutter and flat roof applications.

CARATTERISTICHE

Cable connection: Axial

Connection cable: 4 x 0.5 mm²

Temperature range for moisture measurement: -20°C to 30°C

SPECIFICHE

Table 1/2

Codice a catalogo	Nome articolo	Comunicazione	Profondità	Area pericolosa	Altezza	Classificazione IP
1244-022799	E650C-R-BRACKET-CU	No	80 mm	No	2 mm	IP68
1244-022798	E650C-R-BRACKET-ZN	No	80 mm	No	2 mm	IP68
1244-022795	E650C-R	No	96 mm	No	14 mm	IP68

Table 2/2

Codice a catalogo	Nome articolo	Gamma di misurazione	Larghezza
1244-022799	E650C-R-BRACKET-CU		132 mm

Codice a catalogo	Nome articolo	Gamma di misurazione	Larghezza
1244-022798	E650C-R-BRACKET-ZN		132 mm
1244-022795	E650C-R	-20 to 30 °C	14 mm

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
thermal.info@nvent.com

Il nostro straordinario portafoglio di marchi:

RAYCHEM PYROTENAX TRACER NUHEAT