

Outdoor Comline ECL Cabinet

Strømforsyning



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism ensuring operational continuity.

SERTIFISERINGER



FUNKSJONER

IP 55

Heat dissipation through natural convection

Single wall, lightweight aluminium cabinet

SPESIFIKASJONER

Table 1/2

Katalognummer	Product Type	Product Family	Rack Height	Høyde	Bredde	Dybde
12349-001	Outdoor Cabinet	Comline ECL	12 U	600 mm	600 mm	500 mm
12349-009	Outdoor Cabinet	Comline ECL	12 U	600 mm	600 mm	500 mm
12349-002	Outdoor Cabinet	Comline ECL	18 U	900 mm	600 mm	500 mm

Katalognummer	Product Type	Product Family	Rack Height	Høyde	Bredde	Dybde
12349-003	Outdoor Cabinet	Comline ECL	18 U	900 mm	700 mm	600 mm
12349-010	Outdoor Cabinet	Comline ECL	18 U	900 mm	600 mm	500 mm
12349-011	Outdoor Cabinet	Comline ECL	18 U	900 mm	700 mm	600 mm
12349-004	Outdoor Cabinet	Comline ECL	25 U	1200 mm	700 mm	600 mm
12349-012	Outdoor Cabinet	Comline ECL	25 U	1200 mm	700 mm	600 mm

Table 2/2

Katalognummer	Wall Type	Door Type	Access	Kjøling	EMC Shielding	Samsvarer med
12349-001	Single Walled	Single Door	Front	Natural Convection	Nei	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-009	Single Walled	Single Door	Front	Natural Convection	Nei	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-002	Single Walled	Single Door	Front	Natural Convection	Nei	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

Katalognummer	Wall Type	Door Type	Access	Kjøling	EMC Shielding	Samsvarer med
12349-003	Single Walled	Single Door	Front	Natural Convection	Nei	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-010	Single Walled	Single Door	Front	Natural Convection	Nei	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-011	Single Walled	Single Door	Front	Natural Convection	Nei	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-004	Single Walled	Single Door	Front	Natural Convection	Nei	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-012	Single Walled	Single Door	Front	Natural Convection	Nei	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE