

TT3000 Conductive Liquids Sensing Cable, Modular



nVent RAYCHEM TraceTek TT3000-XX-MC are a range of fixed length modular leak detection cables with metal connectors, used to detect spills and leaks of conductive liquids, including waste water, acids, bases and hazardous waste streams. Installed with an alarm and locating module, the cable senses aqueous chemical leaks, triggers an alarm and pinpoints the location. The cable is designed for a variety of applications, including floor surfaces, subfloors, equipment locations, pipes, storage tanks, and trenches.

CARATTERISTICHE

Advanced technology: conductive polymer & fluoropolymer construction, mechanically strong and resistant to chemicals

Simple and fast to install: small, lightweight and flexible

Easy to design

Distributed leak detection and location over a wide range of areas

Reliable and durable: 5 year product warranty available

SPECIFICHE

Diametro esterno:	6 mm
Max Operating Temperature:	85 °C
Detection:	Conductive Liquids and Aqueous Chemicals
Detection Method:	Raychem Conductive-Polymer Technology
Model:	Sensing Cable

Table 1/1

Numero catalogo	Nome articolo	Lunghezza
148983-000	TT3000-0.3M/1FT-MC	0.3 m
301795-000	TT3000-30M/100FT-MC	30 m
262789-000	TT3000-1.5M/5FT-MC	1.5 m

Numero catalogo	Nome articolo	Lunghezza
492017-000	TT3000-60M/200FT-MC	60 m
048179-000	TT3000-15M/50FT-MC	15 m
103619-000	TT3000-7.5M/25FT-MC	7.5 m
792293-000	TT3000-4.5M/15FT-MC	4.5 m
842667-000	TT3000-3M/10FT-MC	3 m

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT