

19" Front Panel, Plastic



19" plastic made clip on Front Panels with esthetic design are specially made for the datacom vertical. The easy clip on panels help in air flow management and also simultaneously providing an appealing look for the network rack.

CERTIFICAZIONI



CARATTERISTICHE

Attractive design

Simple fitting by clipping onto the 19" plane

SPECIFICHE

Tipo di accessorio: Pannello frontale

Table 1/3

Codice a catalogo	Tipo	Montaggio	Schermatura EMC	Materiale	Finitura anteriore	Finitura posteriore
87927-991	Pannello frontale da 19"	Inserito	No	ABS	Grezzo	Grezzo
87927-992	Pannello frontale da 19"	Inserito	No	ABS	Grezzo	Grezzo
23130-622	Pannello frontale da 19"	Inserito	No	ABS		
23130-623	Pannello frontale da 19"	Inserito	No	ABS		

Table 2/3

Codice a catalogo	Codice colore	Altezza del rack	Altezza	Larghezza rack	Larghezza	Profondità
87927-991	RAL 7035	1U	43.71mm	95HP	482mm	12mm
87927-992	RAL 7035	2U	88.17mm	95HP	482mm	12mm
23130-622	RAL 9005	6U	266.6mm	95HP	483mm	2mm
23130-623	RAL 7035	6U	266.6mm	95HP	483mm	2mm

Table 3/3

Codice a catalogo	Quantità nella confezione	Spedizione rapida
87927-991	10	No
87927-992	10	No
23130-622	10	No
23130-623	10	No

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE