


Minipac Rectangular Shape Case, Desktop

CODICE A CATALOGO

24814-024



The rectangular Alu-profile case enables a user to insert 4 standard PCBs (height 100 mm x depth 160 mm). The PCBs will be inserted in grooves in the Alu-profile tube. Both sides are covered with 2.5 mm thick front panels.

CERTIFICAZIONI



CARATTERISTICHE

Accommodates 4 standardized PCBs (height 100 mm, depth 160 mm) or rotated by 90° to accommodate 8 non-standardized PCBs (height 60 mm, depth 160 mm)

PCB thickness 1.6 mm, spacing 10.16 mm (2 HP)

Length D = 160 mm, long side 110.9 mm, short side 70.3 mm

Desktop version

ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Custodia a fattore di forma ridotto

Famiglia di prodotti: Minipac

Tipo: Desktop

Altezza: 112.3mm

Larghezza: 71.7mm

Profondità: 160.5mm

Materiale: Alluminio

Colore: Nero

Finitura: Anodizzato

Grado di protezione: IP40

Raffreddamento: Non perforato

Forma: Rettangolare

Quantità nella confezione: 1

Lunghezza: 160.5mm

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Other dimensions on request:

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE