



Guida orizzontale, posteriore, tipo L-ST, leggera, standard, 28 CV

CODICE A CATALOGO

34560-428



Combinations of horizontal rails and side panels

		Combinations of horizontal rails and side panels			
		+ = compatible, - = not recommended			
Horizontal rail	ST	-	+	+	+
	ST-L	+	+	+	+
Side panel	ST	+	+	-	-
	ST-L	+	+	-	-

The horizontal rail, type ST enables the isolated assembly of a backplane. The isolation is done by an insulation strip.

CERTIFICAZIONI



CARATTERISTICHE

For indirect backplane mounting with insulation strip

Mounting top and bottom

Aluminum extrusion, anodized finish, conductive contact surface

ATTRIBUTI DEL PRODOTTO

Larghezza rack: 28HP

Quantità nella confezione: 1

Finitura: Anodizzato

Lunghezza: 147.32mm

Materiale: Alluminio

Famiglia di prodotti: EuropacPRO; RatiopacPRO; ARIA RatiopacPRO; CompacPRO; PropacPRO

Tipo di prodotto: Guida orizzontale

Tipo: Leggera, ST

Funziona con: Subracks; Casi

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE