

# Varistar CP Rear Panel with Mounting Plate, Shortened



Shortened rear panel with mounting plate now available as a complete SKU for better cable management.

## CARATTERISTICHE

Screw fixed, Robust and Single person mountable Side Panel

Height of connection plate 400 mm

The height of the rear panel is 400 mm less than the cabinet height

Interior galvanized

## SPECIFICHE

**Tipo di prodotto:** Pannello per armadio/rack

**Grado di protezione:** IP55

**Materiale:** Acciaio inossidabile

Table 1/1

Codice a catalogo	Altezza del rack	Altezza	Larghezza	Quantità nella confezione	Finitura	Spedizione rapida
21630-378	38U	1800mm	600mm	1	Verniciato a polvere	No
21630-379	38U	1800mm	800mm	1	Verniciato a polvere	No
21630-380	42U	2000mm	600mm	1	Verniciato a polvere	No
21630-381	42U	2000mm	800mm	1	Verniciato a polvere	No

Codice a catalogo	Altezza delrack	Altezza	Larghezza	Quantità nella confezione	Finitura	Spedizione rapida
21630-382	47U	2200mm	600mm	1	Verniciato a polvere	No
21630-383	47U	2200mm	800mm	1	Verniciato a polvere	No

## INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Please purchase the grounding kit separately.

## AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Il nostro straordinario portafoglio di marchi:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**