

Socket Strip, SCHUKO, With Wieland® Input



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

SERTIFISERINGER



FUNKSJONER

Installation height 1 U

Output via SCHUKO sockets

Input via Wieland® GST 18 plug

Socket strips can be rotated through all four directions (in 90° increments) during installation

Horizontal or vertical mounting

In accordance with DIN 57620

SPESIFIKASJONER

Lengde:	438.5mm
Materiale:	Aluminium; Polyamid
Produkttype:	Sokkelskinne

Table 1/2

Katalognummer	Kontakttype	Antall kontakter	Utganger med bryter	Spennings AC	Funksjon	Antall pakker
60110-354	SCHUKO	6	Nei	230V	Overstrømsvern	1

Katalognummer	Kontakttype	Antallkontakter	Utganger med bryter	Spenning AC	Funksjon	Antall pakker
60110-353	SCHUKO	6	Nei	230V	Overstrømsvern	1
60110-343	SCHUKO	8	Nei	230V		1
60110-352	SCHUKO	6	Nei	230V	Overstrømsvern	1
60110-345	SCHUKO	8	Nei	230V		1
60110-344	SCHUKO	8	Nei	230V		1

Table 2/2

Katalognummer	Farge	Dybde	Overflate	Hurtiglevering
60110-354	Rød	44mm	Anodisert	Nei
60110-353	Svart	44mm	Anodisert	Nei
60110-343	Grå	44mm	Anodisert	Nei
60110-352	Grå	44mm	Anodisert	Nei
60110-345	Rød	44mm	Anodisert	Nei
60110-344	Svart	44mm	Anodisert	Nei

YTTERLIGERE PRODUKTDETALJER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE