

# Attrezzatura per installazione verticale serie T.



T-Series vertical installation equipment kits contain the following: Pouring basin frame, crucible frame set (crucible chain assembly, crucible extension, crucible cover), two end alignment fittings and a bottom support clamp. Installation equipment kits contain components that are long lasting and often interchangeable with other sizes. Ordering installation equipment kits simplifies ordering, reduces order errors and helps ensure proper sizing of components.

## CARATTERISTICHE

Simplifies ordering

Used to splice the same diameter bars

All components are designed for an extended life

## SPECIFICHE

Table 1/1

Codice a catalogo	Materiale	Dimensione armatura, metrica	Dimensioni armatura, USA	Dimensioni armatura, Canada
RBW7395V	Acciaio, Graphite	16 mm	# 5	15 MLN
RBW7396V	Acciaio, Graphite	20 mm	# 6	20 MLN
RBW7397V	Acciaio, Graphite	22 mm	# 7	
RBW7398V	Acciaio, Graphite	25 mm	# 8	25 MLN
RBW7399V	Acciaio, Graphite	28 mm	#9	30 MLN
RBW73910V	Acciaio, Graphite	32 mm	# 10	
RBW73911V	Acciaio, Graphite	36 mm	#11	35 MLN


Codice a catalogo	Materiale	Dimensione armatura, metrica	Dimensioni armatura, USA	Dimensioni armatura, Canada
RBW73914V	Acciaio, Graphite	43 mm	#14	45 MLN
RBW73918V	Acciaio, Graphite	57 mm	# 18	55 MLN

## INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

Components can also be purchased separately: (1) Pouring Basin Frame, (2) Crucible Chain Assembly, (3) Crucible Extension, (4) Crucible Cover, (5) End Alignment Fitting, and (6) Bottom Support Clamp.

## SCHEMI



## AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

**Nord America**

+1.800.753.9221

Opzione 1 – Assistenza  
clienti

Opzione 2 – Assistenza  
tecnica

**Europa**

Paesi Bassi:

+31 800-0200135

Francia:

+33 800 901 793

**Europa**

Germania:

800 1890272

altri paesi:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Il nostro straordinario portafoglio di marchi:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**