


# Novastar Rear Panel Full Height

## Servizi di distribuzione di energia



Steel Rear Panel for aluminum extruded enclosure is connected with 2 twist-locking catches (Torx T30, with 1/4 turn).

### CERTIFICAZIONI



### CARATTERISTICHE

Incl. grounding

2 twist-locking catches (Torx T30, with 1/4 turn)

St, 1 mm

### SPECIFICHE

Table 1/1

| Numero catalogo | Altezza | Larghezza | Colore | Color Code | Product Type | Tipo |
|-----------------|---------|-----------|--------|------------|--------------|------|
|-----------------|---------|-----------|--------|------------|--------------|------|

|           |         |        |            |          |                    |            |
|-----------|---------|--------|------------|----------|--------------------|------------|
| 25230-370 | 323 mm  | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 26230-370 | 323 mm  | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 25230-371 | 422 mm  | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 26230-371 | 422 mm  | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 25230-147 | 1345 mm | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-372 | 555 mm  | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-373 | 733 mm  | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-374 | 911 mm  | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-375 | 1133 mm | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-376 | 1534 mm | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-377 | 1711 mm | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-378 | 1933 mm | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-379 | 2111 mm | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 26230-147 | 1345 mm | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-372 | 555 mm  | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-373 | 733 mm  | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-374 | 911 mm  | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-375 | 1133 mm | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-376 | 1534 mm | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |

|           |         |        |            |          |                    |            |
|-----------|---------|--------|------------|----------|--------------------|------------|
| 26230-377 | 1711 mm | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-378 | 1933 mm | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-379 | 2111 mm | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |

## ADDITIONAL PRODUCT DETAILS

Optional locking with key (2233x).

## AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**