

Varistar CP Double Steel Door, Perforated With 3-Point Electronic Locking

Servizi di distribuzione di energia

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

CARATTERISTICHE

Double perforated steel door with 3-point locking for IP 20 protection class

Lever handle with push button, key

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with DIN profile half cylinder

SPECIFICHE

Table 1/3

Numero catalogo	Rack Height	Altezza	Larghezza	Colore	Color Code	È conforme a
21630-820	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-821	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-822	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-823	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-824	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-825	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3

Numero catalogo	Finitura	Locking Type	Materiale	Product Type	Protection Rating	Tipo
21630-820	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20	Steel Double Door, Perforated
21630-821	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20	Steel Double Door, Perforated
21630-822	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20	Steel Double Door, Perforated
21630-823	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20	Steel Double Door, Perforated
21630-824	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20	Steel Double Door, Perforated
21630-825	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20	Steel Double Door, Perforated

Table 3/3

Numero catalogo	Works With
21630-820	Varistar CP
21630-821	Varistar CP
21630-822	Varistar CP
21630-823	Varistar CP
21630-824	Varistar CP
21630-825	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE