

Varistar CP Seismic Base/Plinth

Instalacje zasilające

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

FUNKCJE

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

OKREŚLENIU SPECYFIKACJI

Table 1/2

Numer katalogowy	Szerokość	Głębokość	Kolor	Color Code	Zgodność z	Wysokość
21630-110	600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-111	600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-112	600 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-113	600 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-114	800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-115	800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-117	800 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm

Numer katalogowy	Szerokość	Głębokość	Kolor	Color Code	Zgodność z	Wysokość
21630-116	800 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	800 mm

Table 2/2

Numer katalogowy	Materiał	Product Type	Obciążenie statyczne	Typ	Works With
21630-110	Stal	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-111	Stal	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-112	Stal	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-113	Stal	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-114	Stal	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-115	Stal	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-117	Stal	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-116	Stal	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE