

FS Self-Regulating Heating Cable



nVent RAYCHEM FS self-regulating trace heating cables provide energy efficient and easy to use solutions for pipe freeze protection. FS-C10-2X resists higher temperatures and is used for frost protection of dormant central heating pipes.

CARATTERISTICHE

Simple to design

Easy to install: cut to length, meter marks, fast RayClic cold connection system

Energy efficient and safe: self-regulating cable, advanced energy saving controls, no overheating possible

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICHE

Table 1/3

Numero catalogo	Nome articolo	Supply Voltage	Tensione nominale	Nominal Power Output @ 5°C, 230V	Outer Jacket Material	Max Circuit Length
P000000732	FS-C10-2X	220 – 240 V	230 V	10 W/m	Modified Polyolefin	180 m

Table 2/3

Numero catalogo	Nome articolo	Circuit Breaker	Colore	Nominal Width	Nominal Height	Ground Path Type
P000000732	FS-C10-2X	Type C/20Amp	Plum	16 mm	6.8 mm	e collegamento

Table 3/3

Numero catalogo	Nome articolo	Area Classification	Nominal Cable Weight	Max Continuous Exposure Temperature, Power On	Max Continuous Exposure Temperature, Power Off	Max Cumulative Hours for Intermittent Exposure

P000000732	FS-C10-2X	Non-Hazardous	140 g/m	90 °C	90 °C	800 h
------------	-----------	---------------	---------	-------	-------	-------

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT