

# NGC-30 Series, Controller Board



nVent RAYCHEM NGC-30 Series - Controller Board are card rack controller board modules that provide temperature input (RTD), alarms and switching for up to five heat tracing circuits. Available with either electromechanical (NGC-30-CRM) or solid state relays (NGC-30-CRMS).

## CARATTERISTICHE

Easy to install

Mounted in the NGC-30 panel inside the Card Rack

## SPECIFICHE

<b>Corrente nominale:</b>	0.4 A
<b>Tensione nominale:</b>	12 V
<b>Altezza:</b>	89.9 mm
<b>Larghezza:</b>	248 mm
<b>Tipo di tensione nominale:</b>	CC

Table 1/1

Codice a catalogo	Nome articolo	Tipo di relè di controllo
10720-009	NGC-30-CRMS-E	Stato solido
10720-001	NGC-30-CRM	Elettromeccanico
10720-004	NGC-30-CRMS	Stato solido

Codice a catalogo	Nome articolo	Tipo di relè di controllo
10720-008	NGC-30-CRM-E	Elettromeccanico

## AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

**North America**  
 Tel +1.800.545.6258  
 Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East, Africa**  
 Tel +32.16.213.511  
 Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**  
 Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**Latin America**  
 Tel +1.713.868.4800  
 Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Il nostro straordinario portafoglio di marchi:

**RAYCHEM PYROTEX TRACER NUHEAT**