

TT1100-OHP Water Sensing Cable for Suspended Piping, Modular



nVent RAYCHEM TraceTek TT1100-XX-OHP is a range of fixed length water detecting cable intended for use on the bottom side of suspended or rack mounted pipe. The outer layer of the sensor cable is designed to act like a wick so that even small leaks are drawn into contact with the cable to assure detection. TT1100-OHP is also very useful in dirty areas where contamination can cause problems.

CARATTERISTICHE

Advanced technology: synthetic fiber braid, designed to wick water along the cable even when the water leak is dripping from a single small pin hole or crack

Simple and fast to install: strap directly to the pipe, eliminate drip trays

Easy to design: rapid drying, so that once the leak is located and repaired it will be ready for re-use

Distributed leak detection and location over a wide range of areas

SPECIFICHE

Diametro esterno:	8,2 mm
Max Operating Temperature:	80 °C
Detection Method:	Raychem Conductive-Polymer Technology
Model:	Sensing Cable
Detection:	Water

Table 1/1

Numero catalogo	Nome articolo	Lunghezza
P000000809	TT1100-OHP-15M-PC	15 m
P000000811	TT1100-OHP-3M-PC	3 m
P000000808	TT1100-OHP-30M-PC	30 m

Numero catalogo	Nome articolo	Lunghezza
P000000806	TT1100-OHP-100M-PC	100 m
P000000807	TT1100-OHP-50M-PC	50 m
P000001378	TT1100-OHP-5M-PC	5 m
P000000810	TT1100-OHP-7.5M-PC	7.5 m
P000000812	TT1100-OHP-1M-PC	1 m

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT