

Mains Cable



nVent SCHROFF Mains cable provides practical, universal fastening with variable attachment facilities. They are general in nature and fit in to different applications like Fans, cabinet lights, etc., Industrial PC connections, Uninterruptible power supplies, Systems.

CERTYFIKATY



FUNKCJE

Applications: Fans, cabinet lights, Industrial PC connections, Uninterruptible power supplies and Systems

SPECYFIKACJE

Typ produktu: Kabel

Table 1/2

Numer katalogowy	Złącze wejściowe	Złącze wyjściowe	Długość	Liczba opakowań	Kolor	Typ złącza
60103-131	SCHUKO / UTE	IEC C13	2500mm	1	Szary	Proste
62150-191	SCHUKO / UTE	IEC C13	2500mm	1	Czarny	Proste
60110-361	IEC C14	IEC C13	1000mm	1	Czarny	Proste
60103-141	US = standard amerykański	IEC C13	2500mm	1	Czarny	Proste

Numer katalogowy	Złącze wejściowe	Złącze wyjściowe	Długość	Liczba opakowań	Kolor	Typ złącza
60110-360	IEC C14	IEC C13	500mm	1	Czarny	Proste
60704-020	SCHUKO / UTE	IEC C13	2500mm	1	Szary	Układ kątowy
60197-053	IEC C14	IEC C13	2500mm	1	Czarny	Proste
60103-137	BS = standard brytyjski	IEC C13	2500mm	1	Czarny	Proste

Table 2/2

Numer katalogowy	Materiał	Szybka wysyłka
60103-131	PVC	Nie
62150-191	PVC	Nie
60110-361	PVC	Nie
60103-141	PVC	Nie
60110-360	PVC	Nie
60704-020	PVC	Nie
60197-053	PVC	Nie
60103-137	PVC	Nie

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE