


VPX Backplane, 6 U, 10 Slots, BKP6-CEN10-11.2.4-4 RTM

CODICE A CATALOGO

23001-816



The nVent SCHROFF VPX Backplane have excellent Signal Integrity for highest data transfer rates.

CERTIFICAZIONI



CARATTERISTICHE

In accordance with: VITA 46.0 VPX base standard; VITA 46.3 Serial RapidIO on VPX; VITA 46.4 PCI Express on VPX Fabric Connector; VITA 46.7 Ethernet on VPX Fabric Connector; VITA 46.11 System Management for VPX

DIP switch for system slot settings

JTAG connections

Lockable aux utility and sense connectors

M4 power studs for power supply, max. 22 A per slot for each voltage

ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Backplane

Numero di scanalature: 10

Altezza del rack: 6U

Tipo di backplane: VPX, VITA 65

Larghezza asola: 5HP

Tipo di connettore: MultiGig

Tipo di connettore di alimentazione: Powerstuds M4

Tipo di connettore di servizio: Microfit, 8 pin

Larghezza: 262.55mm

Quantità nella confezione: 1

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Other VPX Backplanes and custom VPX Backplane designs on request.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE