

# Varistar CP EMC Shortened Door with Recessed Mounting Plate



Recessed connection plates are needed for connectors which don't protrude out of the plane of the cabinet

## CARATTERISTICHE

Intelligent cable management design with recessed connection plates

Door with lever handle with push button

Door opening angle 180°

Connection plate is 400 mm high

For recessed plate: Plate recessed by 40 mm

## SPECIFICHE

<b>Tipo di prodotto:</b>	Sportello dell'armadio
<b>Grado di protezione:</b>	IP55
<b>Tipo di bloccaggio:</b>	Bloccaggio a più punti
<b>Materiale:</b>	Acciaio; Stainless Acciaio

Table 1/1

Codice a catalogo	Altezza del rack	Altezza	Larghezza	Quantità nella confezione	Finitura	Spedizione rapida
21630-903	38U	1800mm	600mm	1	Verniciato a polvere	No
21630-904	38U	1800mm	800mm	1	Verniciato a polvere	No
21630-905	42U	2000mm	600mm	1	Verniciato a polvere	No

Codice a catalogo	Altezza delrack	Altezza	Larghezza	Quantità nella confezione	Finitura	Spedizione rapida
21630-906	42U	2000mm	800mm	1	Verniciato a polvere	No
21630-907	47U	2200mm	600mm	1	Verniciato a polvere	No
21630-908	47U	2200mm	800mm	1	Verniciato a polvere	No

## AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Il nostro straordinario portafoglio di marchi:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**