nVent LENTON

We connect and protect

Horizontal Pouring Basin, Side Fill



Side fill horizontal pouring basins are used when interferences of the structure will not allow top filling of the sleeve.

CARACTERISTICAS

Made from heat-resistant graphite

Durable, re-usable and long lasting

Designed for use with T-Series and B-Series horizontal side fill sleeves

ESPECIFICAÇÕES

Material: Graphite

Table 1/1

Número de catálogo	Diâmetro (Ø)	Comprimento 1 (L1)	Comprimento 2 (L2)	Largura (W)	Altura 1 (H1)	Altura 2 (H2)
RBWS1547F	64 mm	140 mm	22 mm	76 mm	137mm	67mm
RBWS1547J	76 mm	140 mm	22 mm	76 mm	137mm	67mm
RBWS1547E	57 mm	140 mm	22 mm	76 mm	137mm	67mm
RBWS1547M	95 mm	140 mm	22 mm	76 mm	137mm	67mm
RBWS1547C	48 mm	140 mm	22 mm	76 mm	137mm	67mm
RBWS1547D	54 mm	140 mm	22 mm	76 mm	137mm	67mm

Número de catálogo	Diâmetro (Ø)	Comprimento 1 (L1)	Comprimento 2 (L2)	Largura (W)	Altura 1 (H1)	Altura 2 (H2)
RBWS1547X	38 mm	140 mm	22 mm	76 mm	137mm	67mm

DETALHES ADICIONAIS DO PRODUTO

RBWS1547 pouring basins require one RBW332 pouring basin frame (sold separately).

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System Instruction Manual.

Sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte
+1 800 753 9221
Opção 1 – Apoio ao cliente
Opção 2 – Assistência técnica

Europa
Países Baixos:
+31 800-0200135
França:
+33 800 901 793

Europa
Alemanha:
800 1890272
Outros países:
+31 13 5835404

APAC
Xangai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

O nosso forte portefólio de marcas:
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.