

# Reinforcing Steel Cleaning Brush



The reinforcing steel cleaning brush is used to prepare reinforcing steel for use with nVent LENTON Cadweld. The brush is designed to remove rust, mill scale, dirt and paint in as little as five seconds.

## CARACTERISTICAS

Designed for use with a 3/4", heavy duty, low-speed drill (200-350 rpm)

Cleans reinforcing steel bar, including the bar end

## ESPECIFICAÇÕES

**Material:** Aço

Table 1/1

| Número de catálogo | Tamanho da viga de reforço, metric | Tamanho da viga de reforço, EUA | Tamanho da viga de reforço, Canadá | Diâmetro (Ø) | Length (L) |
|--------------------|------------------------------------|---------------------------------|------------------------------------|--------------|------------|
| RBW34311           | 36 mm                              | #11                             | 35M                                | 114 mm       | 244mm      |
| RBW34318           | 57 mm                              | #18                             | 55M                                | 127 mm       | 206mm      |
| RBW34314           | 43 mm                              | #14                             | 45M                                | 127 mm       | 181mm      |

## DETALHES ADICIONAIS DO PRODUTO


Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

Brushes must be kept free of grease, oil and other contaminants that could evolve gas and cause porosity in the filler material.

Do not reverse the cleaning brush while it is engaged with the reinforcing steel bar.

Eye protection should be used when using power-driven cleaning brushes.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221  
Opção 1 – Apoio ao cliente  
Opção 2 – Assistência técnica

Europa

Países Baixos:  
+31 800-0200135  
França:  
+33 800 901 793

Europa

Alemanha:  
800 1890272  
Outros países:  
+31 13 5835404

APAC

Xangai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



O nosso forte portefólio de marcas:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE