


Verticale plug-in railsteunen voor stroomverdeling, MSVH



These vertical plug-in distribution busbar supports, MSVH, should be mounted on the enclosure behind the plug-in cover. They are available of the shelf and tested according to IEC 61439.

KENMERKEN

Omschrijving: Busbar supports up to 1600A to be mounted vertically behind the plug-in compartments. Rated short-time withstand current up to 35KA with rear supports and up to 50KA with rear and front supports. Mounts to the vertical profiles included in the rear cover plate for plugin sections MSSB.

Materiaal: Polycarbonate reinforced with 10% of glass material.

Levering: 4 busbar support with mounting material.

The supports should be mounted onto the plug-in system vertical profiles (MSSB)

Plug-in busbars (MSBS), must be used in conjunction with these supports

Busbar supports up to 1600A to be mounted vertically behind the plug-in compartments

Rated short-time withstand current up to 35KA with rear supports and up to 50KA with rear and front supports

Mounts to the vertical profiles included in the rear cover plate for plugin sections MSSB

Delivery: 4 busbar support with mounting material

SPECIFICATIES

Table 1/1

Catalogusnummer	Hoogte	Breedte	Diepte	Materiaal van de behuizing	Productfamilie	Materiaal
MSVH1800	40mm	482mm	45mm	Zacht staal	Vrijstaand	Polycarbonaat
MSVH1800F	40mm	482mm	45mm	Zacht staal	Vrijstaand	Polycarbonaat
MSVH2000	40mm	482mm	45mm	Zacht staal	Vrijstaand	Polycarbonaat
MSVH2000F	40mm	482mm	45mm	Zacht staal	Vrijstaand	Polycarbonaat
MSVH2200	40mm	482mm	45mm	Zacht staal	Vrijstaand	Polycarbonaat
MSVH2200F	40mm	482mm	45mm	Zacht staal	Vrijstaand	Polycarbonaat

AANVULLENDE PRODUCTGEGEVENS

*In: Rated current. *Ick: Rated short-time withstand current.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE