

Guide Rail With Coding for CompactPCI/VME64x, PC

Concessionárias de energia

New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

RECURSOS

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to a optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

Optional ESD clip for an conductive contact between PCB and horizontal rail available

Storage temperature: from -40 °C ... 130 °C

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Material	Cor	Package Quantity	Board Depth	Groove Width	Em conformidade com
24568-356	Polycarbonato	Vermelho		160 mm	2	EN 45545-2
24568-357	Polycarbonato	Vermelho		70 mm	2	EN 45545-2

Número do catálogo	Material	Cor	Package Quantity	Board Depth	Groove Width	Em conformidade com
24568-358	Polycarbonato	Grey		160 mm	2	EN 45545-2
24568-360	Polycarbonato	Grey		70 mm	2	EN 45545-2
64568-085	Polycarbonato	Vermelho	50	70 mm	2	EN 45545-2
64568-086	Polycarbonato	Grey	50	70 mm	2	EN 45545-2
64568-091	Polycarbonato	Vermelho	50	220 mm	2	EN 45545-2
64568-092	Polycarbonato	Grey	50	220 mm	2	EN 45545-2
64568-111	Polycarbonate, Aluminum	Red, Silver	50	220 mm	2,5	EN 45545-2
64568-112	Polycarbonate, Aluminum	Grey, Silver	50	220 mm	2,5	EN 45545-2
64568-110	Polycarbonate, Aluminum	Grey, Silver	50	160 mm	2,5	EN 45545-2
64568-109	Polycarbonate, Aluminum	Red, Silver	50	160 mm	2,5	EN 45545-2

Table 2/2

Número do catálogo	Product Family	Product Type	Tipo	Works With
24568-356	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-357	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems

Número do catálogo	Product Family	Product Type	Tipo	Works With
24568-358	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-360	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-085	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-086	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-091	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-092	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-111	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-112	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems

Número do catálogo	Product Family	Product Type	Tipo	Works With
64568-110	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-109	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE