


Novastar Glass Door, 180° Opening Angle

Concessionárias de energia



Glazed / Glass doors for aluminum frame cabinets with attractive design, ideally suited for general electronics, test & measurement, audio/video and broadcasting applications.

CERTIFICAÇÕES



RECURSOS

Glass type: ESG 6 mm, EN 12150

Opening angle 180°

Lock with key

Can be assembled at front and rear

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Rack Height	Altura	Largura	Cor	Color Code	Product Type
27230-001	6 U	323 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
27230-002	9 U	422 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
27230-003	12 U	555 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
27230-004	16 U	733 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
27230-005	20 U	911 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
27230-006	25 U	1133 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
27230-028	29 U	1345 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
27230-007	34 U	1534 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
27230-008	38 U	1711 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
27230-009	43 U	1933 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
27230-010	47 U	2111 mm	553 mm	Light Grey	RAL 7035	Cabinet Door

Table 2/2

Número do catálogo	Tipo
27230-001	Glass Door
27230-002	Glass Door
27230-003	Glass Door
27230-004	Glass Door
27230-005	Glass Door

Número do catálogo	Tipo
27230-006	Glass Door
27230-028	Glass Door
27230-007	Glass Door
27230-008	Glass Door
27230-009	Glass Door
27230-010	Glass Door

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE