


# Horizontal Rail, Front, Type L-KD, Light, Short Lip, 84 HP

## Power Utilities

### CATALOGUSNUMMER

**34560-184**



Combinations of horizontal rails and side panels

|                                                                   | Standard rail | Standard rail with short lip (L-KD) | Standard rail with short lip (L-KD) and side panel | Standard rail with short lip (L-KD) and side panel with short lip |
|-------------------------------------------------------------------|---------------|-------------------------------------|----------------------------------------------------|-------------------------------------------------------------------|
| Standard rail                                                     | -             | +                                   | +                                                  | +                                                                 |
| Standard rail with short lip (L-KD)                               | +             | +                                   | +                                                  | +                                                                 |
| Standard rail with short lip (L-KD) and side panel                | +             | +                                   | -                                                  | -                                                                 |
| Standard rail with short lip (L-KD) and side panel with short lip | +             | +                                   | -                                                  | -                                                                 |

Legend: + = can be combined, - = combination not recommended

The horizontal rail with a short lip makes a clean design to the assembled front panel.

### CERTIFICERINGEN



### KENMERKEN

Standard rail at the front

Installation at top and bottom

Short lip (L-KD)

< 28 HP not to print

Aluminum extrusion, anodized finish, conductive contact surface

### PRODUCTKENMERKEN

Producttype: Horizontale rail

Productfamilie: EuropacPRO; RatiopacPRO; RatiopacPRO LUCHT; CompacPRO; PropacPRO

Type: Licht, KD

Rekbreedte: 84 HP

Lengte: 431.8 mm

Pakkethoeveelheid: 1

## AANVULLENDE PRODUCTGEGEVENS

---

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WAARSCHUWING

---

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op [www.nvent.com](http://www.nvent.com) en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**