

EuropacPRO 19" Subrack Kit for DIN Connector, Slide Rail, Retrofit Shielding

Energiebedrijven



Non-shielded subrack for Din Connector mounting EN 60603-2 , Subrack can be assembled on slide rails to support the subrack inside a cabinet.

CERTIFICERINGEN



KENMERKEN

Subrack with side panel type F ("flexible"), 19" bracket with notch for slide rail assembly

Installed load up to 11 kg

Subrack can be used with slide rails

Horizontal rails, rear, for connector mounting (IEC 60603-2 / DIN 41612)

Threaded insert pre-fitted

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Diepte	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-192	3 U	235 mm	1	DIN Connector	160 mm, 220 mm	Roestvrij staal

Catalogusnummer	Rack Height	Diepte	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-193	3 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Roestvrij staal
24553-194	3 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Roestvrij staal
24553-492	6 U	235 mm	1	DIN Connector	160 mm, 220 mm	Roestvrij staal
24553-493	6 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Roestvrij staal
24553-494	6 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Roestvrij staal

Table 2/3

Catalogusnummer	Handle Included	Montage	Voltoet aan	EMC Shielding	Product Type	Rack Width
24553-192	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24553-193	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24553-194	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24553-492	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24553-493	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24553-494	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP

Table 3/3

Catalogusnummer	Statische belasting
24553-192	11 kgf
24553-193	11 kgf
24553-194	11 kgf
24553-492	11 kgf

Catalogusnummer	Statische belasting
24553-493	11 kgf
24553-494	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE