

Varistar CP Steel Door, Perforated With Multi-Point Locking

Concessionárias de energia

EMC doors with good contact with the frame and gasket to achieve high attenuation.

The 4 point locking helps achieve necessary contact to avoid EMI effects on electronics.

RECURSOS

Perforated door with 4-point locking for EMC applications

Interior galvanized

Opening angle 180°

Lever handle with push button

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Rack Height	Altura	Largura	Cor	Color Code	Locking Type
21630-533	24 U	1200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-534	24 U	1200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-535	29 U	1400 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-536	29 U	1400 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-537	33 U	1600 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-538	33 U	1600 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-539	38 U	1800 mm	600 mm	Black Grey	RAL 7021	4-Point Locking

Número do catálogo	Rack Height	Altura	Largura	Cor	Color Code	Locking Type
21630-540	38 U	1800 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-541	42 U	2000 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-542	42 U	2000 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-543	47 U	2200 mm	600 mm	Black Grey	RAL 7021	5-Point Locking
21630-544	47 U	2200 mm	800 mm	Black Grey	RAL 7021	5-Point Locking

Table 2/2

Número do catálogo	Material	Product Type	Tipo
21630-533	Aço	Cabinet Door	Steel Door, Perforated
21630-534	Aço	Cabinet Door	Steel Door, Perforated
21630-535	Aço	Cabinet Door	Steel Door, Perforated
21630-536	Aço	Cabinet Door	Steel Door, Perforated
21630-537	Aço	Cabinet Door	Steel Door, Perforated
21630-538	Aço	Cabinet Door	Steel Door, Perforated
21630-539	Aço	Cabinet Door	Steel Door, Perforated
21630-540	Aço	Cabinet Door	Steel Door, Perforated
21630-541	Aço	Cabinet Door	Steel Door, Perforated
21630-542	Aço	Cabinet Door	Steel Door, Perforated
21630-543	Aço	Cabinet Door	Steel Door, Perforated
21630-544	Aço	Cabinet Door	Steel Door, Perforated

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE