

Interscale Mounting Plate With Built-In Fan Holder and Fans

Energiebedrijven

Interscale mounting plate with built-in fan holder and fans, for desktop cases and 19" chassis. Available in different sizes and with three fan versions, with a air flow volume from 10 to 170 m3/h.

KENMERKEN

Mounting plate (raised 4 mm) with integrated fan holder including fan kit for perforated case versions

Fans are simple to fit to the mounting plate using vibrationdamping fixing material

Mounting plate fixes into desktop case with 4 plastic feet or into 19" case with 4 screws

For technical data of fans, please see delivery includes

SPECIFICATIES

Table 1/2

Catalogusnummer	Breedte	Diepte	Hoogte	Materiaal	Product Family	Product Type
24827-105	444 mm	177 mm	1 mm	Staal	Interscale	Mounting Plate
24827-107	444 mm	310 mm	1 mm	Staal	Interscale	Mounting Plate
24827-154	221 mm	177 mm	1 mm	Staal	Interscale	Mounting Plate
24827-155	221 mm	221 mm	1 mm	Staal	Interscale	Mounting Plate
24827-175	310 mm	221 mm	1 mm	Staal	Interscale	Mounting Plate
24827-195	399 mm	221 mm	1 mm	Staal	Interscale	Mounting Plate
24827-197	399 mm	310 mm	1 mm	Staal	Interscale	Mounting Plate

Catalogusnummer	Breedte	Diepte	Hoogte	Materiaal	Product Family	Product Type
24827-255	221 mm	221 mm	1 mm	Staal	Interscale	Mounting Plate
24827-275	310 mm	221 mm	1 mm	Staal	Interscale	Mounting Plate
24827-295	399 mm	221 mm	1 mm	Staal	Interscale	Mounting Plate
24827-297	399 mm	310 mm	1 mm	Staal	Interscale	Mounting Plate
24827-375	310 mm	221 mm	1 mm	Staal	Interscale	Mounting Plate
24827-395	399 mm	221 mm	1 mm	Staal	Interscale	Mounting Plate
24827-397	399 mm	310 mm	1 mm	Staal	Interscale	Mounting Plate
24827-254					Interscale	Mounting Plate
24827-205						Mounting Plate
24827-207						Mounting Plate
24827-305						Mounting Plate
24827-307						Mounting Plate

Table 2/2

Catalogusnummer	Rack Width	Type	Works With
24827-105	19 HP	Mounting Plate	Small Form Factor Cases
24827-107	19 HP	Mounting Plate	Small Form Factor Cases
24827-154		Mounting Plate	Small Form Factor Cases
24827-155		Mounting Plate	Small Form Factor Cases
24827-175		Mounting Plate	Small Form Factor Cases

Catalogusnummer	Rack Width	Type	Works With
24827-195		Mounting Plate	Small Form Factor Cases
24827-197		Mounting Plate	Small Form Factor Cases
24827-255		Mounting Plate	Small Form Factor Cases
24827-275		Mounting Plate	Small Form Factor Cases
24827-295		Mounting Plate	Small Form Factor Cases
24827-297		Mounting Plate	Small Form Factor Cases
24827-375		Mounting Plate	Small Form Factor Cases
24827-395		Mounting Plate	Small Form Factor Cases
24827-397		Mounting Plate	Small Form Factor Cases
24827-254		Mounting Plate	
24827-205			
24827-207			
24827-305			
24827-307			

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE