


Novastar Side Panel for Heavy-Duty

Energiebedrijven



Steel Side Panels for Heavy-Duty aluminum frame with quick fastener for easy mounting and installation. Schroff delivers cladding parts with grounding cable installed and tested.

CERTIFICERINGEN



KENMERKEN

With quick-release fastener, includes grounding

St. 1mm

SPECIFICATIES

Table 1/2

Catalogusnummer	Rack Height	Hoogte	Diepte	Kleur	Color Code	Product Type
25230-067	12 U	531 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel

Catalogusnummer	Rack Height	Hoogte	Diepte	Kleur	Color Code	Product Type
25230-068	12 U	531 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-222	12 U	531 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-272	12 U	531 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-067	12 U	531 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-068	12 U	531 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-222	12 U	531 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-272	12 U	531 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-322	12 U	531 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-069	16 U	709 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-080	16 U	709 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-223	16 U	709 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-273	16 U	709 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-323	16 U	709 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-069	16 U	709 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-080	16 U	709 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-223	16 U	709 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-273	16 U	709 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-323	16 U	709 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel

Catalogusnummer	Rack Height	Hoogte	Diepte	Kleur	Color Code	Product Type
25230-103	20 U	887 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-104	20 U	887 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-224	20 U	945 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-274	20 U	945 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-324	20 U	945 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-103	20 U	887 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-104	20 U	887 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-224	20 U	945 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-274	20 U	945 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-324	20 U	945 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-105	25 U	1109 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-106	25 U	1109 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-225	25 U	1167 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-275	25 U	1167 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-325	25 U	1167 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-105	25 U	1109 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-106	25 U	1109 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-225	25 U	1167 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel

Catalogusnummer	Rack Height	Hoogte	Diepte	Kleur	Color Code	Product Type
26230-275	25 U	1167 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-325	25 U	1167 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-107	34 U	1509 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-108	34 U	1509 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-226	34 U	1567 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-276	34 U	1567 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-326	34 U	1567 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-107	34 U	1509 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-108	34 U	1509 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-226	34 U	1567 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-276	34 U	1567 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-326	34 U	1567 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-109	38 U	1687 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-110	38 U	1687 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-227	38 U	1745 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-277	38 U	1745 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-327	38 U	1745 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-109	38 U	1687 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel

Catalogusnummer	Rack Height	Hoogte	Diepte	Kleur	Color Code	Product Type
26230-110	38 U	1687 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-227	38 U	1745 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-277	38 U	1745 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-327	38 U	1745 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-111	43 U	1909 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-112	43 U	1909 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-228	43 U	1967 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-278	43 U	1967 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-328	43 U	1967 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-111	43 U	1909 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-112	43 U	1909 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-228	43 U	1967 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-278	43 U	1967 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-328	43 U	1967 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-040	47 U	2087 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-041	47 U	2087 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-229	47 U	2145 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-279	47 U	2145 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel

Catalogusnummer	Rack Height	Hoogte	Diepte	Kleur	Color Code	Product Type
25230-329	47 U	2145 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-040	47 U	2087 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-041	47 U	2087 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-229	47 U	2145 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-279	47 U	2145 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-329	47 U	2145 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-322		531 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel

Table 2/2

Catalogusnummer	Type	Breedte
25230-067	Side Panel	
25230-068	Side Panel	
25230-222	Side Panel	
25230-272	Side Panel	
26230-067	Side Panel	
26230-068	Side Panel	
26230-222	Side Panel	
26230-272	Side Panel	
26230-322	Side Panel	
25230-069	Side Panel	

Catalogusnummer	Type	Breedte
25230-080	Side Panel	
25230-223	Side Panel	553 mm
25230-273	Side Panel	553 mm
25230-323	Side Panel	553 mm
26230-069	Side Panel	
26230-080	Side Panel	
26230-223	Side Panel	553 mm
26230-273	Side Panel	553 mm
26230-323	Side Panel	553 mm
25230-103	Side Panel	
25230-104	Side Panel	
25230-224	Side Panel	553 mm
25230-274	Side Panel	553 mm
25230-324	Side Panel	553 mm
26230-103	Side Panel	
26230-104	Side Panel	
26230-224	Side Panel	553 mm
26230-274	Side Panel	553 mm

Catalogusnummer	Type	Breedte
26230-324	Side Panel	553 mm
25230-105	Side Panel	
25230-106	Side Panel	
25230-225	Side Panel	553 mm
25230-275	Side Panel	553 mm
25230-325	Side Panel	553 mm
26230-105	Side Panel	
26230-106	Side Panel	
26230-225	Side Panel	553 mm
26230-275	Side Panel	553 mm
26230-325	Side Panel	553 mm
25230-107	Side Panel	
25230-108	Side Panel	
25230-226	Side Panel	553 mm
25230-276	Side Panel	553 mm
25230-326	Side Panel	553 mm
26230-107	Side Panel	
26230-108	Side Panel	

Catalogusnummer	Type	Breedte
26230-226	Side Panel	553 mm
26230-276	Side Panel	553 mm
26230-326	Side Panel	553 mm
25230-109	Side Panel	
25230-110	Side Panel	
25230-227	Side Panel	553 mm
25230-277	Side Panel	553 mm
25230-327	Side Panel	553 mm
26230-109	Side Panel	
26230-110	Side Panel	
26230-227	Side Panel	553 mm
26230-277	Side Panel	553 mm
26230-327	Side Panel	553 mm
25230-111	Side Panel	
25230-112	Side Panel	
25230-228	Side Panel	553 mm
25230-278	Side Panel	553 mm
25230-328	Side Panel	553 mm

Catalogusnummer	Type	Breedte
26230-111	Side Panel	
26230-112	Side Panel	
26230-228	Side Panel	553 mm
26230-278	Side Panel	553 mm
26230-328	Side Panel	553 mm
25230-040	Side Panel	
25230-041	Side Panel	
25230-229	Side Panel	553 mm
25230-279	Side Panel	553 mm
25230-329	Side Panel	553 mm
26230-040	Side Panel	
26230-041	Side Panel	
26230-229	Side Panel	553 mm
26230-279	Side Panel	553 mm
26230-329	Side Panel	553 mm
25230-322	Side Panel	

ADDITIONAL PRODUCT DETAILS

Optionally the quarter-turn fastener can be fitted with a side panel lock.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE